




Dimensions



Awards



Name	LEX MINI ASYMM DALI TUNABLE WHITE Z
Reference	A3790028Z
Colour	Aluminium
RAL	9006
Category	CEILING RECESSED
Type	LED
Gross luminous flux	1250 lm
Colour temperature	Tunable White 2700 - 5000 K
Chromatic stability	MacAdam Step 3
Colour Rendering Index	CRI>90
Power	10,5 W
Current	600 mA
Efficacy	119 lm/W
LED lifespan	L90B10 >55.000h
Energy efficiency class	F
Lighting efficiency	70%
Light beam angle	64°
Driver	Included
Power values of the system	13,46 W
Frequency	50/60 Hz
Dimming	DALI - Other DIM, please consult
Electrical insulation class	<input type="checkbox"/>
Sealing	IP20
Wireless control	Please Consult
Emergency power supply	Please Consult
Recess measurements	Ø105 mm
Weight	458 g
Packaged weight	603 g
Packaging dimensions	194 x 163 x 119 mm
Units per package	1
Materials	Aluminium / Polycarbonate
OTHER DATA	
Sealing	IP20
Wireless control	Please Consult
Emergency power supply	Please Consult
Recess measurements	Ø105 mm
Weight	458 g
Packaged weight	603 g
Packaging dimensions	194 x 163 x 119 mm
Units per package	1
Materials	Aluminium / Polycarbonate

PRODUCT

LEX MINI ASYMM DALI TUNABLE WHITE Z

A3790028Z

Aluminium

9006

CEILING RECESSED

LIGHT SOURCE

LED

1250 lm

Tunable White 2700 - 5000 K

MacAdam Step 3

CRI>90

10,5 W

600 mA

119 lm/W

L90B10 >55.000h

F

LIGHTING FIXTURE | PHOTOMETRIC DATA

70%

64°

LIGHTING FIXTURE | ELECTRICAL DATA

Included

13,46 W

50/60 Hz

DALI - Other DIM, please consult



OTHER DATA

IP20

Please Consult

Please Consult

Ø105 mm

458 g

603 g

194 x 163 x 119 mm


1

Aluminium / Polycarbonate



Lex Mini is the smaller version of Lex. Like its big brother, it offers high visual comfort thanks to the double setback of its LED which is located further back in the luminaire, and housed, too, at the end of a second screen. Its mini size is coherent with its proportions, harmonious in relation to its power and flux.

Polar diagram



cd/klm
 — C0 - C180 — C90 - C270

$\eta = 66\%$

Conical diagram



Distance [m] Cone Diameter [m] Illuminance [lx]
 — C90 - C270 (Half-value Angle: 63,9°) — C0 - C180 (Half-value Angle: 60,7°)



Fuente de luz (LED) reemplazable por un profesional autorizado
 Replaceable (LED only) light source by an authorized professional.
 Source lumineuse (LED) remplaçable par un professionnel agréé
 Sorgente luminosa (LED) sostituibile da parte di un professionista autorizzato
 Austauschbare (LED) Lichtquelle durch einen autorisierten Fachmann



Equipo de control reemplazable por un profesional autorizado
 Replaceable control gear by an authorized professional
 Dispositif de commande remplaçable par un professionnel agréé
 Alimentatore sostituibile da parte di un professionista autorizzato
 Auswechselbares Betriebsgerät durch autorisierten Fachmann

Instrucciones para el final de vida y la eliminación de los componentes:

Instructions on end-of-life and component disposal:

Instructions pour la gestion des composants en fin de vie et leur mise au rebut :

Istruzioni per il fine vita e lo smaltimento dei componenti:

Anweisungen zur entsorgung der Leuchtenkomponenten:



Interrumpir la alimentación del aparato
 Cut the power supply to the luminaire
 Couper l'alimentation du luminaire
 Interrompere l'alimentazione dell'apparecchio
 Stromversorgung der Leuchte unterbrechen



Quitar la(s) fuente(s) de luz para el desecho
 Remove light source(s) for disposal
 Retirer la (les) source(s) lumineuse(s) pour l'élimination
 Rimuovere la/le sorgente/e di luce per lo smaltimento
 Lichtquelle(n) zur Entsorgung entfernen



Quitar la batería para el desecho
 Remove the battery for decommissioning
 Retirer la batterie pour sa mise au rebut
 Rimuovere la batteria per la dismissione
 Die Batterie ordnungsgemäß entsorgen



Quitar el equipo de control para el desecho
 Remove control gear for disposal
 Retirer le dispositif de commande pour l'élimination
 Rimuovere l'alimentatore per lo smaltimento
 Betriebsgerät zur Entsorgung ausbauen



Enviar los materiales a un centro de recogida RAEE
 Send the materials to a WEEE collection centre
 Envoyer les matériaux dans une déchetterie DEEE
 Inviare i materiali ad un centro di raccolta RAEE
 Die Materialien in einem WEEE-Zentrum entsorgen

