





DIMENSIONS



AWARDS



Name	BLACK FOSTER MICRO RECESSED 2X2 3000K W
Reference	A4143011W
Color	Textured white - Chrome
RAL	Colour in the mass looks alike RAL 9010
Category	CEILING RECESSED

PRODUCT

Type	LED
Gross luminous flux	640 lm
Colour temperature	3000 K
Chromatic stability	MacAdam Step 3
Colour Rendering Index	CRI > 90
Power	5,6 W
Current	500 mA
Efficacy	114 lm/W
LED lifespan	L90B10 > 60.000h

LIGHT SOURCE

Lighting efficiency	87%
Light beam angle	37°

LIGHTING FIXTURE | PHOTOMETRIC DATA

Driver	Included
Power values of the system	7,37 W
Frequency	50/60 Hz
Dimming	No Dim
Electrical insulation class	□

LIGHTING FIXTURE | ELECTRICAL DATA


Sealing	IP20
Wireless control	Please Consult
Emergency power supply	Please Consult
Recess measurements	42 x 42 mm
Weight	125 g
Packaged weight	200 g
Packaging dimensions	176 x 79 x 50 mm
Units per package	1
Materials	Aluminium / Acrylonitrile Butadiene Styrene / Polycarbonate

OTHER DATA




Black Foster Micro is a feat of engineering which brings the acclaimed 'The Invisible Black' effect to a hyper-reduced light. Its tiny size and thin trim offer a 'trimless visual' aesthetic which combines with its almost imperceptible presence as a result of its compact dimensions. Black Foster Micro is designed for general or accent lighting and can be used in projects that seek ceiling lighting that plays a minimal role.

POLAR DIAGRAM




CONICAL DIAGRAM



UGR

Glare Evaluation According to UGR												
		70	70	50	50	30	70	70	50	50	30	30
p Ceiling		70	70	50	50	30	70	70	50	50	30	30
p Walls		50	30	50	30	30	50	30	50	30	30	30
p Floor		20	20	20	20	20	20	20	20	20	20	20
Room Size X Y		Viewing direction at right angles to lamp axis					Viewing direction parallel to lamp axis					
2H	2H	-4.9	-4.3	-4.7	-4.1	-3.9	-5.6	-5.0	-5.4	-4.8	-4.6	-4.6
	3H	-1.8	-1.2	-1.5	-1.0	-0.8	-1.7	-1.2	-1.5	-0.9	-0.7	-0.7
	4H	-0.1	0.4	0.2	0.6	0.9	0.3	0.8	0.6	1.1	1.3	1.3
	6H	2.1	2.6	2.4	2.9	3.2	2.4	2.9	2.7	3.2	3.5	3.5
	8H	3.3	3.8	3.7	4.1	4.4	3.4	3.9	3.7	4.2	4.5	4.5
4H	2H	-4.1	-3.5	-3.8	-3.3	-3.0	-4.6	-4.0	-4.3	-3.8	-3.5	-3.5
	3H	-0.6	-0.2	-0.3	0.1	0.4	-0.6	-0.1	-0.2	0.2	0.5	0.5
	4H	1.2	1.6	1.6	2.0	2.3	1.6	2.0	2.0	2.4	2.7	2.7
	6H	3.7	4.1	4.1	4.4	4.8	4.0	4.3	4.4	4.7	5.1	5.1
	8H	5.1	5.3	5.5	5.7	6.1	5.1	5.4	5.5	5.8	6.2	6.2
8H	2H	6.3	6.5	6.7	6.9	7.4	6.3	6.6	6.7	7.0	7.4	7.4
	3H	2.1	2.4	2.5	2.8	3.2	2.4	2.7	2.8	3.1	3.5	3.5
	4H	4.8	5.0	5.2	5.4	5.9	5.0	5.2	5.5	5.7	6.1	6.1
	6H	6.3	6.4	6.7	6.9	7.4	6.3	6.5	6.7	6.9	7.4	7.4
	8H	7.7	7.8	8.2	8.3	8.8	7.7	7.8	8.2	8.3	8.8	8.8
12H	4H	2.4	2.6	2.8	3.0	3.4	2.6	2.9	3.1	3.3	3.7	3.7
	6H	5.1	5.3	5.6	5.7	6.2	5.3	5.5	5.8	5.9	6.4	6.4
	8H	6.7	6.8	7.2	7.3	7.8	6.7	6.8	7.2	7.3	7.8	7.8
Variation of the observer position for the luminaire distances S												
S = 1.0H		+6.0 / -4.4					+6.0 / -4.3					
S = 1.5H		+8.8 / -4.8					+8.7 / -4.7					
S = 2.0H		+10.8 / -5.4					+10.8 / -5.0					
Standard table		BK01					BK01					
Correction Summand		-5.3					-5.4					
Corrected Glare Indices referring to 640lm Total Luminous Flux												



Fuente de luz (LED) reemplazable por un profesional autorizado

Replaceable (LED only) light source by an authorized professional.

Source lumineuse (LED) remplaçable par un professionnel agréé

Sorgente luminosa (LED) sostituibile da parte di un professionista autorizzato

Austauschbare (LED) Lichtquelle durch einen autorisierten Fachmann



Equipo de control reemplazable por un profesional autorizado

Replaceable control gear by an authorized professional

Dispositif de commande remplaçable par un professionnel agréé

Alimentatore sostituibile da parte di un professionista autorizzato

Auswechselbares Betriebsgerät durch autorisierten Fachmann

INSTRUCCIONES PARA EL FINAL DE VIDA Y LA ELIMINACIÓN LOS COMPONENTES

INSTRUCTIONS ON END-OF-LIFE AND COMPONENT DISPOSAL

INSTRUCTIONS POUR LA GESTION DES COMPOSANTS EN FIN DE VIE ET LEUR MISE AU REBUT

ISTRUZIONI PER IL FINE VITA E LO SMALTIMENTO DEI COMPONENTI

ANWEISUNGEN ZUR ENTSORGUNG DER LEUCHTENKOMPONENTEN



Interrumpir la alimentación del aparato

Cut the power supply to the luminaire

Couper l'alimentation du luminaire

Interrompere l'alimentazione dell'apparecchio

Stromversorgung der Leuchte unterbrechen



Quitar la(s) fuente(s) de luz para el desecho

Remove light source(s) for disposal

Retirer la (les) source(s) lumineuse(s) pour l'élimination

Rimuovere la/le sorgente/e di luce per lo smaltimento

Lichtquelle(n) zur Entsorgung entfernen



Quitar la batería para el desecho

Remove the battery for decommissioning

Retirer la batterie pour sa mise au rebut

Rimuovere la batteria per la dismissione

Die Batterie ordnungsgemäß entsorgen



Quitar el equipo de control para el desecho

Remove control gear for disposal

Retirer le dispositif de commande pour l'élimination

Rimuovere l'alimentatore per lo smaltimento

Betriebsgerät zur Entsorgung ausbauen

Enviar los materiales a un centro de recogida RAEE

Send the materials to a WEEE collection centre

Envoyer les matériaux dans une déchetterie DEEE

Inviare i materiali ad un centro di raccolta RAEE

Die Materialien in einem WEEE-Zentrum entsorgen

